

The Danfoss product range for Industrial Refrigeration applications

| | Page | |
|---|------|--------------------------------------|
| Stop and regulating valves | 5 | Stop and regulating valves |
| Line Components | 73 | Line Components |
| Solenoid valves | 135 | Solenoid valves |
| Pressure and temperature regulators | 207 | Pressure and temp. regulators |
| Control solutions | 375 | Control solutions |
| Electromechanical controls | 403 | Electromechanical controls |
| Safety valves | 447 | Safety valves |
| Gas detectors | 499 | Gas detectors |
| Expansion valves | 513 | Expansion valves |
| Level controls | 535 | Level controls |
| Electronic controls and transmitters | 599 | Electronic controls and transmitters |

The Danfoss product range for Industrial Refrigeration applications

| | | | |
|---|------|---|------|
| Stop and regulating valves | Page | Safety valves | Page |
| Stop Needle Valve, type SNV-ST and SNV-SS..... | 5 | Safety relief valves, type SFA 15 | 447 |
| Stop valves, type SVA, SVA-ST, SVA-HS and SVA-SS..... | 11 | Safety relief valves, type SFV 20 - 25..... | 455 |
| Stop valves, type SVA-DL & SVA-DH 250-300..... | 35 | Double stop valves, type DSV 1 and DSV 2..... | 465 |
| Quick closing oil drain valve, type QDV 15 | 43 | Safety relief valves, type BSV 8 | 473 |
| Regulating valves, types REG 6 - 65 and REG-SS 15-40..... | 49 | Pilot operated internal safety valves, type POV..... | 483 |
| | | | |
| Stop/check and Check valves | | Gas detectors | |
| Stop check valves type SCA, SCA-SS - Check valves type CHV, CHV-SS..... | 73 | Gas Detection Sensor, type GDA, GDC, GDHC, GDHF, GDH..... | 499 |
| Check valves for ammonia and fluorinated refrigerants, type NRVA | 87 | | |
| Check valve for EVRA, EVRAT and PM valves in liquid lines, type NRVS | 103 | | |
| | | | |
| Filtes and sight glasses | | Expansion valves | |
| Strainers, type FA..... | 107 | Thermostatic expansion valves for ammonia, type TEA | 513 |
| Filter, types FIA and FIA-SS..... | 111 | Thermostatic injection valves, type TEAT | 519 |
| Filter drier with replaceable solid core, type DCR..... | 121 | Electrically operated expansion valves, type AKVA 10, 15 & 20 | 523 |
| Sight glass, type MLI..... | 131 | | |
| | | | |
| Solenoid valves | | Level controls | |
| Solenoid valves type EVRA 3 to 40 and EVRAT 10 to 20..... | 135 | Thermostatic liquid level regulators, type TEVA..... | 535 |
| Stainless steel solenoid valves type EVRS 3 → 20 and EVRST 10 → 20..... | 147 | High pressure float valve, type HFI | 537 |
| Solenoid valve, type PML | 155 | Modulating liquid level regulators, direct-controlled, type SV 1 and 3..... | 547 |
| Solenoid valves, two-step on/off, type PMLX | 171 | Modulating liquid level regulators, direct operated, | |
| Gas powered stop valves, type GPLX 80-150 | 187 | for low pressure side, types SV 4, 5 and 6..... | 557 |
| Coils for solenoid valves..... | 201 | Modulating liquid level regulators, servo-controlled, | |
| | | type PMFL / PMFH and SV | 565 |
| | | Liquid level alarms, safety switches, liquid level regulators, | |
| | | type RT 280A, RT 281A..... | 577 |
| | | Float switch, type AKS 38 | 579 |
| | | Liquid level transmitter, type AKS 41 / 41U..... | 585 |
| | | Liquid level glasses, type LLG 185 - 1550..... | 593 |
| | | | |
| Pressure and temperature regulators | | Electronic controls and transmitters | |
| Pilot controlled servo valves, type ICS..... | 207 | Liquid level controller, type EKC 347 | 599 |
| Motor valves, type ICM and actuators type ICAD | 255 | Media temperature controller, type EKC 361 | 609 |
| Pilot operated main valves | | Interface module, type EKC 366..... | 621 |
| for regulating pressure and temperature, type PM | 303 | Evaporator controller, type EKC 315A..... | 627 |
| Pilot valves for servo operated main valves..... | 327 | Discharge temperature controller, type EKC 319A..... | 639 |
| Constant pressure valve, type CVMD | 345 | Capacity controller, pressure - type EKC 331..... | 645 |
| Overflow valves, type OFV, OFV-SS 20 - 25 | 347 | Capacity controller, temperature - type EKC 331 T..... | 653 |
| Capacity regulators (hot gas bypass), type PMC and CVC..... | 357 | Temperature sensors, type AKS 10..... | 663 |
| Oil regulating valve, type ORV..... | 365 | Temperature sensors, type AKS 11, AKS 12, AKS 21 | 665 |
| | | Pressure transmitters, type AKS 3000 | 667 |
| | | Pressure transmitters, type AKS 32 and AKS 33..... | 671 |
| | | Pressure transmitter with ratiometric output signal, type AKS 32R..... | 675 |
| | | | |
| Control solutions | | | |
| The ICF Control Solution..... | 375 | | |
| | | | |
| Electromechanical controls | | | |
| Thermostats, type KP | 403 | | |
| Thermostats, differential thermostats, type RT | 411 | | |
| Differential pressure controls, type MP 54, 55 and 55A | 423 | | |
| Pressure controls, type KP | 429 | | |
| Pressure controls, differential pressure controls, type RT..... | 437 | | |

The Danfoss product range for Industrial Refrigeration applications

| Type | Page | Type | Page |
|--------------------------------|----------|-----------------------------------|------|
| A | | I | |
| AKS 10 | 663 | ICAD | 255 |
| AKS 11, AKS 12, AKS 21 | 665 | ICF | 375 |
| AKS 3000..... | 667 | ICM..... | 255 |
| AKS 32..... | 671 | ICS | 207 |
| AKS 32R..... | 675 | K | |
| AKS 33..... | 671 | KP - pressostats | 429 |
| AKS 38..... | 579 | KP - thermostats..... | 403 |
| AKS 41, AKS 41U..... | 585 | L | |
| AKVA..... | 523 | LLG | 593 |
| B | | M | |
| BSV | 473 | MLI | 131 |
| C | | MP | 423 |
| CHV, CHV-SS | 73 | N | |
| Coils | 201 | NRVA | 87 |
| CVC | 333, 357 | NRVS..... | 103 |
| CVH..... | 343 | O | |
| CVMD | 345 | OFV, OFV-SS..... | 347 |
| CVP (HP and LP) | 328 | ORV | 365 |
| CVP (M)..... | 339 | P | |
| CVP (XP) | 332 | PM | 303 |
| CVPM..... | 339 | PMC | 357 |
| CVPP (HP and LP)..... | 330 | PMFH, PMFL..... | 565 |
| CVQ..... | 337 | PML..... | 155 |
| CVT, CVTO | 335 | PMLX..... | 171 |
| D | | POV..... | 483 |
| DCR | 121 | Q | |
| DSV | 465 | QDV | 43 |
| E | | R | |
| EKC 315A | 627 | REG, REG-SS | 49 |
| EKC 319A | 639 | RT - pressostats | 437 |
| EKC 331 | 645 | RT - thermostats..... | 411 |
| EKC 331T..... | 653 | RT 280A, RT 281A..... | 577 |
| EKC 347 | 599 | S | |
| EKC 361 | 609 | SCA, SCA-SS..... | 73 |
| EKC 366 | 621 | SFA | 447 |
| EVM (NC)..... | 341 | SFV | 455 |
| EVM (NO) | 341 | SNV-SS, SNV-ST..... | 5 |
| EVRA, EVRAT | 135 | SV 1 and 3..... | 547 |
| EVRS, EVRST | 147 | SV 4, 5 and 6..... | 557 |
| F | | SVA, SVA-HS, SVA-SS, SVA-ST | 11 |
| FA | 107 | SVA-DH, SVA-DL | 35 |
| FIA, FIA-SS | 111 | T | |
| G | | TEA..... | 513 |
| GDA, GDC, GDHC, GDHF, GDH..... | 499 | TEAT | 519 |
| GPLX..... | 187 | TEVA | 535 |
| H | | | |
| HFI..... | 537 | | |

